

Braco Brass PG type Glands are suitable for unarmoured, plastic or rubber sheathed cables. These glands are made from Brass with Nickel Plated.

These Glands provide IP protection upto IP-68 levels. Polyamide Claws with EPDM Rubber can hold cable firmly and have a wider cable Range. Resistant to salt water, Weak acid, Alcohol, Oil, Grease and Common Solvency.



Brass Cable Glands PG Type - (PG & Metric Thread)

Gland Size	Cable OD Range	Thread OD C1	Thread Length C2		Hex Dimension	Gland Size	Cable OD Range	Thread OD C1	Thread Length C2		Hex Dimension
			Short	Long					Short	Long	
BPG- 7	3-6.5	12.5	6	10	14	BPGM-12 x 1.5	3-6.5	M-12	6	10	14
BPG- 7 S	2-5	12.5	6	10	14	BPGM-16 x 1.5	4-8	M-16	7	10	17
BPG-9	4-8	15.2	7	10	17	BPGM-18 x 1.5	5-10	M-18	7	10	20
BPG-9 S	2-6	15.2	7	10	17	BPGM-20 x 1.5	6-12	M-20	7.5	10	22
BPG-11	5-10	18.6	7	10	20	BPGM-22 x 1.5	10-14	M-22	7.5	10	24
BPG-11 S	3-7	18.6	7	10	20	BPGM-24 x 1.5	11-15	M-24	8	12	26
BPG-13.5	6-12	20.4	7.5	10	22	BPGM-25 x 1.5	12-16	M-25	8	12	27
BPG-13.5 S	5-9	20.4	7.5	10	22	BPGM-25 x 1.5	13-18	M-25	8	12	30
BPG-16	10-14	22.5	7.5	10	24	BPGM-27 x 1.5(2)	13-18	M-27	8	12	30
BPG-16 S	7-12	22.5	7.5	10	24	BPGM-30 x 1.5(2)	15-20	M-30	9	12	33
BPG-19	11-15	24	8	12	26	BPGM-32 x 1.5(2)	16-21	M-32	9	12	35
BPG-19 S	10-13	24	8	12	26	BPGM-40 x 1.5(2)	22-32	M-40	9	15	45
BPG- 21	13-18	28.3	8	12	30	BPGM-50 x 1.5(2)	32-38	M-50	10	15	57
BPG- 21 S	9-16	28.3	8	12	30	BPGM-63 x 1.5(2)	37-44	M-63	11	15	68
BPG-25	16-20	30	9	12	33	BPGM-70 x 1.5(2)	42-52	M-70	15	20	80
BPG-25 S	13-18	30	9	12	33	BPGM-72 x 1.5(2)	42-52	M-70	15	20	80
BPG-29	18-25	37	9	12	40	BPGM-75 x 1.5(2)	42-52	M-75	15	20	80
BPG-29 S	13-20	37	9	12	40	BPGM-80 x 1.5(2)	55-62	M-80	15	20	87
BPG-36	22-32	47	9	15	50	BPGM-88 x 1.5(2)	65-70	M-88	15	20	95
BPG-36 S	20-26	47	9	15	50	BPGM-100 x 1.5(2)	78-84	M-100	15	20	110
BPG-42	32-38	54	10	15	57						
BPG-42 S	25-31	54	10	15	57						
BPG-48	37-44	59.3	11	15	64						
BPG-48 S	29-35	59.3	11	15	64						
BPG-63	42-52	72	15	20	80						
BPG-63 S	32-40	72	15	20	80						

BPGM: Metric Thread PG Glands. Suffix 'L' is for Long Nipple

BPG : PG Thread Glands. Suffix 'S' is for smaller dia Rubber, Suffix 'L' is for Long Nipple, Suffix 'SL' is for small rubber is for long Nipple.

